

**3** 3D 3DPEN-2 DRW YOUR DREAM



- prouct:3D PEN-2
- Adapter:100-240V 12V2A
- Net Weight:62g+ -5g
- Nozzle:0.7mm Diameter
- Paingts:ABS/PLA
- Plastic Feeding:1.75mm Diameter

CE FCC ROHS

READ INSTRUCTIONS BEFORE OPERATING

- 3D 3DPEN-2 DRW YOUR DREAM
- 3D 3DPEN-2 DRW YOUR DREAM

- 000000 000000

000000 000

000000:

1. 000 0.7 0000 0000
2. 0000 PLA/ABS 00 1.75 0000
3. 00000000 0000 00 0000
4. 00000 2/0000 12 :000000 0000
5. 00 00000000 0000 00 0000000 00000000 000000 000000 00000 230 - 000000 0000 180 :0000000 0000 00000 00000000 000000
6. 0000 00 000000 0000 00000000000 000000 5 00 0000 00000000 000000 00000000 000000 00000000 0000 00000000 0000000 0000000 0000000 0000000 .0000000 00000 00 00000 00 00000000!

000000 000:



1) 3D pen 1 x 3D logo 1 x 3 pcs \* 3m ( )



Free Filaments



Power Adapter



User Manual







ABS PLA



光ファイバーケーブルの種類と色分け



Develop intelligence

Intelligent thermostat

Dimensional graffiti

Insert the nozzle

Creative fun

Safety





□□□□□ □□

**Function Diagram**



**How to use**

Step1 Insert the end of the charger into the bottom socket power inlet of the 3D pen. Power led will be on, the 3D pen enter into standby mode. (Fig 1)  
 Step2 Select the PLA/ABS status according to the different material. then Click the Feed-in key. Wait for 10~20S the Green Led will be lighted. (Fig2&Fig3)



Step3 Insert the filaments into the Feeding Hole (Fig 4), continue click the Feed-in Key until the melted resin flow out from the nozzle (Fig 5). Now the 3D pen is ready for using. Click the Feed-in key to draw, but if you click the Feed-in Key exceed 5S,the pen will

be in automatic feeding. Click again, it will be back to the manual mode



Step4 The feeding speed can be adjusted by moving the Speed controller forward and backward (Fig 6). the Pen will be in standby mode automatically when not use over 2 minutes (Fig7) Green Led will be off,click the Feed-in key ,it can be used again when the Green Led is lighted.



Step 5 Click the Feed-out Key until the remaining parts are out of the Feeding hole(Fig 8) when the filament is over. Insert the new filament and click the Feed-in key (Repeat step1) it should be noticed that the front shape of the filament is as followings (Fig9)



**Note**

- 1 Do not touch the nib and nozzle, High temperature.
- 2 It is suitable for kids over 5 years old and adult using, it is necessary for kids to use under the guardianship of adult.
- 3 Unload the filament after use and turn off the power

本產品為3D打印筆，適用於PLA/ABS材料。請參閱說明書，並掃描QR碼獲取更多資訊。



本產品為3D打印筆，適用於PLA/ABS材料。請參閱說明書，並掃描QR碼獲取更多資訊。本產品為3D打印筆，適用於PLA/ABS材料。請參閱說明書，並掃描QR碼獲取更多資訊。



# COMPANY INFORMATION

• SELECTECH •

About us



✓ Quality



✓ Experience



✓ Service



✓ Produce



## Selectech Electronics Co.,Ltd

- Welcome to ShenZhen Selectech Electronics Co., Limited. -- Your power sourcing for smart home and home health&beauty care products, consumer electronics, plastics products! Selectech is 11 years gold supplier in alibaba with trade assurance.



Office room



Team picture (1)



Team picture (2)

- Selectech was founded in Shenzhen in year 2005. Selectech invested factories focuses on production and R&D for smart home, home health care Oscope&Camera,home consumer electronics. like Alexa Echo Google home control WiFi smart socket plug, USB charger wall socket receptable,smart fast wall charger, universal travel adapter,ENT otoscope,oral camera, USB&Wireless microscope and endoscope,DLP projector,baby monitor ect.

## Our factory



- Welcome to visit our website and factory to know more. We can supply the mould, R&D, custom and OEM/ODM service as per your request! Over 16 years Experiences in manufacturing & business, support customers with good service of rich experience which will save customer's working time to meet win-win!

Professional manufacturer



WELCOME TO ORDER



- Our aim is: "Top quality, Customer benefit firstly". Our company is based on "Credibility", aimed at "Win-Win" and took "service" as bounden duty. All products are strictly followed ISO9001:2008 and met CE, BSI, FCC, UL and RoHS standard.

## Production process



## Customer photos



- Selectech Electronics is constantly improving itself at the spirit of building brand products and striding towards diversity and scale. Selectech has its own experienced technology engineers, modern management team, strong technical strength, advanced injection and testing machines and perfect quality control system to guarantee the quality, security and punctuality of delivery.



- Looking forward to cooperating with you!  
Selectech is your reliable and the best partner to start your business!

## Certificate



## Our advantages



### Why choose us



16 years OEM&ODM experience.



Custom-made products and packing as per customer's request.



Supply free cost samples.



All goods must be passed QA, QC, FQC inspect and test.



Quickly delivery time. Small qty have stock, Lots qty, it's about 20-25days.



We can supply drop shipping, cheapest and economic Express shipment.



We can collect all goods to ship for our customers.



Supply after-sales and quality guarantee service.



With FCC, CE, ETL, ROHS quality certification.



With ISO9001 Quality management system.

Shipping choice



Shipping choice



### FAQ

1. How long does it take to ship to the United States?

It takes 7-10 business days to ship to the United States. Shipping to other countries may take longer.

2. How long does it take to ship to Europe?

It takes 10-15 business days to ship to Europe. Shipping to other countries may take longer.

3. How long does it take to ship to Australia?

It takes 15-20 business days to ship to Australia. Shipping to other countries may take longer. We offer a 24-hour customer support service to help you with any shipping questions.

