

Product Features:

□□ □□□ :

□□ : □□□ □□□ □ □□□□ □□ □□ □□□□ □□□□ □□□ □□□□

□□□ □□ □□□□ CPU. USB □□□ □□□ USB OTG□ □□□□ □□□ □□□ □□ (□ - □ - □□)

00. 000 00 USB "000"000 0000 000 00 (USB 00000)

OTG) □ □ □ □ □ □ □ □ 4.1.2 □ □.

□□□□□□ □□ :
□□

□□□□□□ □□□□ □□□ □□□□ □□□□□□□□ □□□□□ □□□□ □□ :

□□ □□□□ : □□ □□ □□ □□

□□ : □□□□□□ □□

Mac 〇〇〇〇 〇〇 :

Mac

[illegible]

Windows 10000 00 :

CD 00 000 0 0000. 00 000 0 0000 00 0 0000 00 0000 00 00 0000 :

SE-12U200A - 2.0M UVC LED, UVC LED array module

□□ □ □□ □□□□

USB MICROSCOPE 100x 1000x. 100x 1000x 100x 1000x

□□ □□, □□□ □□, □□□□, □□ □□ □□ □□

□□□□ □□□□. □□□ USB □□□□□ □□ □ □□□ □□ □

□□□ □□□ □□□□ □□□□ □□□□□ □□□□ □□ □□□□.

USB 000000 00, 00, 000, 00, 00 0000 0000 00 000 000,

□ □□, □□, □□, □□, □□ □□□ □ □□□□ □□ □□□ □□□ □□ □□

□□ □□□□□□. □□ □□□ PC □□□□□ □□□ □□□.

00 00 0000 0000 000 0 000, 0 0000 0000 00.

□ □ □ □

1. DSP : 1000 1000 1000 1000 1000.
2. 100 : 1000 CMOS 100, 2.0M 100
3. 1000 : 1600 × 1200
4. 100000 : USB2.0.
5. 1000 100 : 30 1000 / 10 (CIF 10 VGA).
6. 100 100 : 5mm - ∞
7. 100 : 1 10 - (17 "100 640 × 480100 10000 5mm100) 200 ×
8. USB 1000 100 : 1.5 m
- 9 : 100 12mm, 100 140mm

□□ LIST

USB 1 1000 * 1

$$\square\square\square\square \cdot \square\square\square\square * 1$$
$$1000 \times 1$$
$$\square\square\square\square \square\square * 1$$

```
□ specula * 1
```

$\square \square \square * 1$
 OTG $\square \square \square * 1$
 CD $* 1$

□□ □□ □□□ □□□ □□ □□□□ □□□□□ 15mm □□□ □□ □□□ □□□□□□ □□ □□□ □□. □□ □□□ □□□ □□ □□ □□□□ □□□□□□.



MULTI-FUNCTION

[illegible]

□□□ □□□ □□□ □□□ □□ □ □□ □□□ □□□ □ 25mm□□.

我们可以在 `main` 函数中，通过 `mainThread` 变量来访问主线程的 `RunLoop`。然后，我们可以在 `mainThread` 的 `RunLoop` 中，通过 `mainThread.runLoop()` 方法来启动主线程的 `RunLoop`。最后，我们可以在 `mainThread` 的 `RunLoop` 中，通过 `mainThread.isDone` 属性来判断主线程的 `RunLoop` 是否已经运行完毕。

CAPS ☐ ☐

□□□ □□ □□□ □□ □□□ □□□□□ □□ □□□□ □□ □ □ □□□

[illegible]

□□□ □□□, □□□ □□□ □□ □ □□ □□□ □□□ 20mm□□.



EAR

It is a long, thin, silver-colored metal probe with a white, flared, cone-shaped tip. It is used for ear examinations. It is a long, thin, silver-colored metal probe with a white, flared, cone-shaped tip. It is used for ear examinations. It is a long, thin, silver-colored metal probe with a white, flared, cone-shaped tip. It is used for ear examinations.



Product

It is a long, thin, silver-colored metal probe with a white, flared, cone-shaped tip. It is used for ear examinations. It is a long, thin, silver-colored metal probe with a white, flared, cone-shaped tip. It is used for ear examinations. It is a long, thin, silver-colored metal probe with a white, flared, cone-shaped tip. It is used for ear examinations.



Product Pictures:



More models and specification to choose:

Tube	Picture	Model No.	Pixel	Resolution	Diameter	Length	Zoom	Feature	Assessory
12mm		SE-12U200-2.0M	2.0M	1600 X 1200	12mm	140mm	1X-200X	USB type	• 1 x pen Microscope • 1 x Reflector • 1 x focusing cap • 1x Ear specula • 1 x tube • 1 x CD (including the manual and dpc) • 1 x Stand
		SE-12U200A-2.0M						USB type& Mobile type (Android system)	
		SE-12AV200-0.3M	0.3M	640 x 480	12mm	140mm	1X-200X	AV type	
8mm		SE-8U300-2.0MW (With adjustable Working Station Stand)	2.0M	1600 X 1200	8mm	170mm	1X-300X	USB type	*1 x 8mm Microscope *1 x Reflector tube *2 x Ear Specular *2 x nose Specular *1x waterproof metal tube (OD:9.5mm) *1 x CD (including manual and dpc) *1 x Stand
		SE-8U300-2.0MR (With Universal Rotation adjustable stand)							
		SE-8AV300-0.3MW (With adjustable Working Station Stand)	0.3M	640 x 480	8mm	170mm	1X-300X	AV type	
		SE-8AV300-0.3MR (With Universal Rotation adjustable stand)							

Product Packaging:

GW / G.W : 27 KGS

NW / N.W : 26 KGS

MEAS : 55x40x40 CM

：

USB	1
	1
	1
	1
	1
	1

□ □ □	1
□ □ □ □ □ CD (□ □ □ □ □ □ □ □)	1

Approval Certification:



Why Choose US :

Our goal is to provide customers products of high quality, competitive price, and superior services.

- 1.Established in 2005, about 10 years of history;
- 2.Own main factories, supply diversification products and One stop service
- 3.Certificates of ISO9001, UL, CE, EMC,CQC,RoHS,Reach,etc.
- 4.Six years Gold member in Alibaba, Aliexpress etc
- 5.Production capability more than 100 thousands pcs/ month;
- 6.Monthly export more than 50 times delivery;
- 7.Exported to more than 20 countries and regions;
- 8.We provide an excellent combination between prices, quality & respond,delivery,after-sales!

Order program

Selectech

